

**Garant**
**Solid carbide HPC drill Weldon shank DIN 6535 HB, TiAlN, Ø DC h7: 14mm**

**Order data**

Order number	123102 14
GTIN	4045197458902
Item class	11E

**Description**
**Version:**

Cutting chisel edge with **high centring accuracy** due to **strong core and special point geometry**.

Particularly high alignment accuracy due to **4 guide chamfers** which stabilise the drill even at extreme depths!

**Convex cutting edges** with honed edges and special flute profile for **short chips**, even on long chipping materials.

**Advantage:**

**High process reliability and surface quality of the hole.**

**Note:**

Flute length  $L_c = L_2 + 1.5 \times D_c$ .

**NEW GENERATION AVAILABLE!**

**Recommended successor products are No. 123026 and 123036.**

**Technical description**

Flute length $L_c$	131 mm
Feed $f$ in steel $< 1100 \text{ N/mm}^2$	0.26 mm/rev.
Number of cutting edges $Z$	2
Shank tolerance	h6
Nominal $\varnothing D_c$	14 mm
Tolerance nominal $\varnothing$	h7
Shank $\varnothing D_s$	14 mm
Overall length $L$	178 mm

Standard	Manufacturer's standard
recommended maximum drilling depth L <sub>2</sub>	110 mm
Coating	TiAlN
Tool material	Solid carbide
Version	8×D
Point angle	135 degrees
Shank	DIN 6535 HB to h6
Through-coolant	yes, with 25 bar
Machining strategy	HPC
Semi-Standard	yes
Colour ring	green
Type of product	Jobber drill

## User data

	Suitability	V <sub>c</sub>	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	180 m/min	N
Alu > 10% Si	suitable only under restricted conditions	140 m/min	N
Steel < 500 N/mm <sup>2</sup>	suitable only under restricted conditions	110 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	90 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	80 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	50 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable	35 m/min	P
INOX < 900 N/mm <sup>2</sup>	suitable only under restricted conditions	40 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable only under restricted conditions	35 m/min	M
GG(G)	suitable	70 m/min	K

Uni	suitable
wet maximum	suitable