




Solid carbide milling cutter with more chip separators TPC, TiAlN, Ø f8 DC: 8mm



Order data

| | |
|--------------|---------------|
| Order number | GG3095 8 |
| GTIN | 4062406333935 |
| Item class | GGN |

Description

Version:

High-performance milling cutter specially designed for general-purpose TPC applications. Strengthened core.

Optimised bending strength due to the use of ultra-fine grain substrates.

Chip separator for controlled chip breaking.

Same as No. 203095.

Note:

h_{\max} : The values stated in the table are maximum values.

$a_{e\max} = 0.07 \times D$ for TPC machining.

Technical description

| | |
|------------------------------------|-------------------|
| Overall length L | 68 mm |
| Corner chamfer angle | 45 degrees |
| Shank | DIN 6535 HB to h6 |
| Overhang length L_1 incl. recess | 30 mm |
| Balance quality with shank | G 2.5 with HB |

| | |
|---|-------------------------|
| Corner chamfer width at 45° | 0.16 mm |
| Cutting edge $\varnothing D_c$ | 8 mm |
| Recess $\varnothing D_1$ | 7.8 mm |
| Flute length L_c | 24 mm |
| Direction of infeed | horizontal and oblique |
| Average chip thickness h_{max} for TPC milling in Toolox 44 HRC | 0.042 mm |
| Helix angle | 40 degrees |
| Tolerance nominal \varnothing | f8 |
| No. of teeth Z | 5 |
| Shank $\varnothing D_s$ | 8 mm |
| Contents | 5 |
| Coating | TiAlN |
| Tool material | Solid carbide |
| Standard | Manufacturer's standard |
| Type | N |
| Helix angle characteristic | unequal spacing |
| Spacing of the cutters | unequal spacing |
| Cutting width a_e for milling operation | $0.07 \times D$ |
| Through-coolant | no |
| Machining strategy | TPC |
| Colour ring | green |
| Type of product | End / face mill |

User data

| | Suitability | V_c | ISO code |
|-------------------------------|-------------|-----------|----------|
| Steel < 500 N/mm ² | suitable | 380 m/min | P |
| Steel < 750 N/mm ² | suitable | 340 m/min | P |
| Steel < 900 N/mm ² | suitable | 300 m/min | P |

| | | | |
|-------------------------------------|---|-----------|---|
| Steel < 1100 N/mm ² | suitable | 230 m/min | P |
| Steel < 1400 N/mm ² | suitable | 150 m/min | P |
| TOOLOX 33 | suitable | 60 m/min | H |
| TOOLOX 44 | suitable | 40 m/min | H |
| HARDOX 500 < 1600 N/mm ² | suitable | 25 m/min | H |
| INOX < 900 N/mm ² | suitable | 220 m/min | M |
| INOX > 900 N/mm ² | Suitable only under restricted conditions | 150 m/min | M |
| Uni | suitable | | |
| wet maximum | suitable | | |
| dry | Suitable only under restricted conditions | | |
| Air | suitable | | |

Accessories

Solid carbide milling cutter with chip separators TPC Ø f8
DC 8 mm

203095 8