



**HOLEX Pro Steel solid carbide roughing end mill HPC, TiAlN, Ø d11 DC: 10mm**

**Order data**

Order number	GG5704 10
GTIN	4062406335458
Item class	GGN

**Description**
**Version:**

Dimensions similar to DIN 6527. **Optimised special knuckle profile for roughing. Very high metal removal rate.**

**Same as No. 205704.**

**Application:**

For roughing machining, particularly suitable for full-slot machining.

**Technical description**

Helix angle	45 degrees
Corner chamfer width at 45°	0.5 mm
Overall length L	66 mm
Shank Ø D <sub>s</sub>	10 mm
Feed f <sub>z</sub> for slot milling in steel < 900 N/mm <sup>2</sup>	0.05 mm
Feed f <sub>z</sub> for side milling in steel < 900 N/mm <sup>2</sup>	0.06 mm
Corner chamfer angle	45 degrees
Cutting edge Ø D <sub>c</sub>	10 mm

Tolerance nominal $\varnothing$	d11
No. of teeth Z	4
Flute length $L_c$	14 mm
Shank	DIN 6535 HB to h6
Direction of infeed	horizontal, oblique and vertical
Contents	5
Series	Pro Steel
Coating	TiAlN
Tool material	Solid carbide
Standard	DIN 6527
Milling profile	HR
Cutting width $a_e$ for milling operation	Full slot cutting depth $1 \times D$
Cutting width $a_e$ for milling operation	Full slot cutting depth $1 \times D$
Through-coolant	no
Machining strategy	HPC
Colour ring	green
Type of product	End / face mill

## User data

	Suitability	$V_c$	ISO code
Steel < 750 N/mm <sup>2</sup>	suitable	170 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	160 m/min	P
Steel < 1100 N/mm <sup>2</sup>	Suitable	135 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable	120 m/min	P
INOX < 900 N/mm <sup>2</sup>	suitable	60 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable only under restricted conditions	45 m/min	M
GG(G)	suitable	120 m/min	K
Uni	suitable		

wet maximum	suitable
wet minimum	suitable only under restricted conditions
dry	Suitable only under restricted conditions
Air	Suitable only under restricted conditions

---

## Accessories

HOLEX Pro Steel solid carbide roughing end millHPC Ø d11  
DC 10 mm

205704 10