## Garant

#### Fluteless machine tap with oil grooves HSS-E-PM Form C 6GX, TiN, M: M3



### **Order data**

Order number	139190 M3
GTIN	4045197509338
Item class	11H

### Description

#### Version:

DIN 2174 ( $\approx$  DIN 371  $\leq$  M10;  $\approx$  DIN 376  $\geq$  M12). With oil grooves; optimum lubrication effect even in deeper threads. Tolerance class: ISO 3X / 6GX = Oversize 0.02 – 0.04 mm. The innovative polygon form permits a wide application spectrum. The multi-function layer structure achieves maximum service life even in high-tensile materials. Application: For components which are galvanised after threading or which shrink slightly when hardened. Tolerance class: ISO 3X 6GX Thread pitch: 0.5 mm Overall length L: 56 mm Shank Ø D;: 3.5 mm

# Tapping hole Ø with guide value: 2.8 mm

### **Technical description**

Thread pitch	0.5 mm
Number of clamping slots	3
Thread Ø	3 mm
Number of cutting edges Z	3
Shank Ø D <sub>s</sub>	3.5 mm
Shank square 🗆	2.7 mm
Overall length L	56 mm

© Hoffmann GmbH Qualitätswerkzeuge

Tapping hole $\varnothing$ with guide value	2.8 mm
Tolerance class	ISO 3X 6GX
Thread depth	9 mm
Thread size	M3
Coating	TiN
Thread type	М
Flank angle	60 degrees
Tool material	HSS E PM
Standard	DIN 2174
Thread standard	DIN 13
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for blind holes and through holes
Cutting direction	right-hand
Colour ring	green
Type of product	Fluteless tap