



Solid carbide high performance drill Weldon shank DIN 6535 HB, TiN, Ø DC h7: 11,5mm



Order data

Order number	122635 11,5
GTIN	4045197395085
Item class	12E

Description

Version:

Cutting chisel edge with **high centring accuracy** due to **strong core and special point geometry**.

Straight major cutting edges with slightly honed edges and special flute profile produce **short chips**.

Note:

Flute length $L_c = L_2 + 1.5 \times D_c$.

NEW GENERATION AVAILABLE!

Recommended successor product is No. 122777.

Technical description

Flute length L_c	71 mm
Shank tolerance	h6
Number of cutting edges Z	2
Nominal $\varnothing D_c$	11.5 mm
Feed f in steel < 900 N/mm ²	0.22 mm/rev.
Tolerance nominal \varnothing	h7
Shank $\varnothing D_s$	12 mm
Overall length L	118 mm
Standard	DIN 6537

recommended maximum drilling depth L_2	53.8 mm
Coating	TiN
Tool material	Solid carbide
Version	6xD
Point angle	140 degrees
Shank	DIN 6535 HB to h6
Through-coolant	yes, with 25 bar
Colour ring	green
Type of product	Jobber drill

User data

	Suitability	V_c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	240 m/min	N
Steel < 500 N/mm ²	suitable	110 m/min	P
Steel < 750 N/mm ²	suitable	90 m/min	P
Steel < 900 N/mm ²	suitable	80 m/min	P
Steel < 1100 N/mm ²	suitable only under restricted conditions	65 m/min	P
Steel < 1400 N/mm ²	suitable only under restricted conditions	30 m/min	P
INOX < 900 N/mm ²	suitable	35 m/min	M
INOX > 900 N/mm ²	suitable	30 m/min	M
Ti > 850 N/mm ²	suitable	30 m/min	S
Uni	suitable		
wet maximum	suitable		
wet minimum	suitable		
Air	suitable only under restricted conditions		

