



Cordless beveller handheld, Type: AKFH18-5



Order data

Order number	078124 AKFH18-5
GTIN	
Item class	03F

Description

Version:

For producing chamfers and radii on flat materials, sheet metal and containers, internal and external edges, contour profiles and for rounding off holes.

Powerful cordless beveller for optimum preparation of the following coatings for flexible working in the workshop and on the construction site. Cordless beveller up to 5 mm.

Supplied with:

1 machine incl. 45° milling head (without guide roller, without indexable inserts), 3 clamping screws, 1 copper paste, 1 hexagon L-wrench 4 mm, 1 Torx screwdriver TX 15, 1 plastic tool case.

Note:

The necessary accessories can be found in our eShop from No. 078136 – 078138.

See No. 073832 size 9260431501 for suitable battery starter sets.

Technical description

Manufacturer's designation	AKFH 18-5 Select
Weight	3 kg
Chamfer angle	45 °
Number of rechargeable batteries contained	0
No load speed	2400 - 7500 min ⁻¹
Disc Ø	98 mm
Radius	2.5 mm

Battery voltage	18 V
Type of rechargeable battery	Lithium-ion
Power supply	Rechargeable battery-powered
suitable battery - supplier / battery type / voltage	Fein type E 18 V
Packaging	Carrying case
Type of product	Deburring and chamfering machine

Accessories

Insert screw setfor beveller Type 3135007600	078139 3135007600
Indexable insert set Type 6430200201	078138 6430200201
Indexable insert set Type 6430200101	078138 6430200101
Guide roller Type 6430300101	078136 6430300101