



Beveller handheld, Type: KFH17-15R



Order data

Order number	078125 KFH17-15R
GTIN	4014586892733
Item class	03F

Description

Version:

For producing chamfers and radii on flat materials, sheet metal and containers, internal and external edges, contour profiles and for rounding off holes.

General-purpose beveller with booster technology for optimum weld seam preparation and preparation for subsequent coatings. Non-fatiguing working with FEIN **ErgoGrip**. Beveller up to 15 mm

Including **spring technology**: Absorption of rotational forces and thus increased safety at work due to low-vibration working.

Supplied with:

1 machine (without milling head, without guide roller, without indexable inserts), 6 clamping screws, 1 copper paste, 1 hexagon L-wrench 5 mm, 1 Torx screwdriver TX 15, 1 plastic tool case.

Note:

The necessary accessories can be found in our eShop from No. 078136 – 078138.

Technical description

Weight	6.4 kg
Power consumption	1700 W
Radius	3 mm
Manufacturer's designation	KFH 17-15 R
Cable length	4 m

Disc Ø	137 mm
Chamfer angle	30 degrees
Chamfer angle	45 degrees
No load speed	2300 - 7500 min ⁻¹
Power supply	Mains operated
Packaging	Carrying case
Type of product	Deburring and chamfering machine

Accessories

Indexable insert set Type 6430200401	078138 6430200401
Indexable insert set Type 6430200601	078138 6430200601
Guide roller Type 6430300401	078136 6430300401
Insert screw setfor beveller Type 3135007500	078139 3135007500
Guide roller Type 6430300201	078136 6430300201
Beveller Type 6430100401	078137 6430100401