

# Fluteless machine tap with oil grooves HSS-E-PM Form C 6GX, TiN, M: M8



### **Order data**

Order number	139190 M8
GTIN	4045197509376
Item class	11H

### Description

#### **Version:**

DIN 2174 ( $\approx$  DIN 371  $\leq$  M10;  $\approx$  DIN 376  $\geq$  M12). With oil grooves; optimum lubrication effect even in deeper threads.

**Tolerance class:** ISO 3X / 6GX =**Oversize 0.02 – 0.04 mm.** 

The innovative polygon form permits a wide application spectrum. The multi-function layer structure achieves maximum service life even in high-tensile materials.

#### **Application:**

For components which are **galvanised after threading** or which shrink slightly when hardened.

Tolerance class: ISO 3X 6GX Thread pitch: 1.25 mm Overall length L: 90 mm Shank Ø D<sub>s</sub>: 8 mm

Shank square □: 6.2 mm

Tapping hole Ø with guide value: 7.45 mm

## **Technical description**

Number of cutting edges Z	5
Thread Ø	8 mm
Thread pitch	1.25 mm
Number of clamping slots	5
Shank Ø D <sub>s</sub>	8 mm
Shank square □	6.2 mm
Overall length L	90 mm

Tapping hole Ø with guide value	7.45 mm
Tolerance class	ISO 3X 6GX
Thread depth	24 mm
Thread size	M8
Coating	TiN
Thread type	M
Flank angle	60 degrees
Tool material	HSS E PM
Standard	DIN 2174
Thread standard	DIN 13
Taper lead form	С
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for blind holes and through holes
Cutting direction	right-hand
Colour ring	green
Type of product	Fluteless tap