



## Solid carbide high performance drill plain shank DIN 6535 HA, TiN, Ø DC h7 (mm or inch): 17



### Order data

Order number	122630 17
GTIN	4045197054449
Item class	12E

### Description

#### Version:

Cutting chisel edge with **high centring accuracy** due to **strong core and special point geometry**.

**Straight major cutting edges** with slightly honed edges and special flute profile produce **short chips**.

#### Note:

Flute length  $L_c = L_2 + 1.5 \times D_c$ .

Form HB and HE supplied at the same price as HA.

Form **HB**: order with **No. 122635**.

Form **HE**: order with **No. 122640**.

**NEW GENERATION AVAILABLE!**

**Recommended successor product is No. 122776.**

### Technical description

Feed f in steel < 900 N/mm <sup>2</sup>	0.28 mm/rev.
Number of cutting edges Z	2
Nominal Ø D <sub>c</sub>	17 mm
Shank tolerance	h6
Flute length L <sub>c</sub>	93 mm
Tolerance nominal Ø	h7
Shank Ø D <sub>s</sub>	18 mm

Overall length L	143 mm
Standard	DIN 6537
recommended maximum drilling depth L <sub>2</sub>	67.5 mm
Coating	TiN
Tool material	Solid carbide
Version	6×D
Point angle	140 degrees
Shank	DIN 6535 HA to h6
Through-coolant	yes, with 25 bar
Semi-Standard	yes
Colour ring	green
Type of product	Jobber drill

## User data

	Suitability	V <sub>c</sub>	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	240 m/min	N
Steel < 500 N/mm <sup>2</sup>	suitable	110 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	90 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	80 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable only under restricted conditions	65 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable only under restricted conditions	30 m/min	P
INOX < 900 N/mm <sup>2</sup>	suitable	35 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable	30 m/min	M
Ti > 850 N/mm <sup>2</sup>	suitable	30 m/min	S
Uni	suitable		
wet maximum	suitable		
wet minimum	suitable		

Air

suitable only under  
restricted conditions