

**Pallet truck, Fork length: 1150mm****Order data**

Order number	919911 1150
GTIN	4062406348717
Item class	96D

Description**Version:**

Hand pallet truck for ergonomic transport of goods.

Frame and forks in distortion-free shell construction. Sturdy steel tube drawbar with thrust bearing for push operation. Convenient moving, lifting and lowering via the ergonomic handle. Tandem polyurethane fork rollers red Ø 80×70 mm, solid rubber castors.

Colour:

RAL 3020 traffic red, **powder-coated.**

Length: 1540 mm

Width: 540 mm

Fork length: 1150 mm

Fork width: 160 mm

Lift range: 85 - 200 mm

Load capacity: 2500 kg

Technical description

Length	1540 mm
Weight	68 kg
Fork width	160 mm

Width	540 mm
Load capacity	2500 kg
Fork length	1150 mm
Lift range	85 - 200 mm
Type of product	Pallet truck