

Garant

Synchronised fluteless machine tap with oil grooves HSS-E-PM IC / Form C, TiN, M: M10



Order data

Order number	139230 M10
GTIN	4045197446985
Item class	11H

Description

Version:

Special polygon geometry and shank to DIN 1835-B for machines with **synchronised spindle drive**. **With oil grooves; optimal lubrication effect even in deeper threads.**

The **innovative polygon form** permits a wide application spectrum. The **multi-function layered coating** achieves **maximum service life** even in **high-tensile materials** in **fixed applications**.

With internal coolant supply laterally from the grooves; permits maximum tool life.

Note:

For use on synchronised spindles, the **GARANT** quick-change tapping chuck **No. 338100 – 338121 with minimum length adjustment (MLA)** ensures the highest process reliability.

Tolerance class: ISO 2X 6HX

Thread pitch: 1.5 mm

Overall length L: 100 mm

Shank $\varnothing D_s$: 10 mm

Shank square \square : 8 mm

Tapping hole \varnothing guide value: 9.35 mm

Technical description

Number of cutting edges Z	5
Number of clamping slots	5
Thread \varnothing	10 mm
Thread pitch	1.5 mm
Shank $\varnothing D_s$	10 mm

Shank square <input type="checkbox"/>	8 mm
Overall length L	100 mm
Tapping hole Ø guide value	9.35 mm
Tolerance class	ISO 2X 6HX
Thread depth	25 mm
Thread size	M10
Coating	TiN
Thread type	M
Flank angle	60 °
Tool material	HSS E PM
Standard	Manufacturer's standard
Thread standard	DIN 13
Taper lead form	C
Shank	DIN 1835 B with h6
Through-coolant	yes
Application for type of drilling	up to 2×D for blind holes
Application for type of drilling	up to 2.5×D for through holes
Cutting direction	right-hand
Shank tolerance	h6
Colour ring	green
Type of product	Fluteless tap

User data

	Suitability	V _c	ISO code
Alu plastics	suitable	48 m/min	N
Aluminium (short chipping)	suitable	48 m/min	N
Alu > 10% Si	suitable only under restricted conditions	45 m/min	N

Steel < 500 N/mm ²	suitable	50 m/min	P
Steel < 750 N/mm ²	suitable	42 m/min	P
Steel < 900 N/mm ²	suitable	40 m/min	P
Steel < 1100 N/mm ²	suitable	37 m/min	P
Steel < 1400 N/mm ²	suitable only under restricted conditions	27 m/min	P
INOX < 900 N/mm ²	suitable	10 m/min	M
CuZn	suitable only under restricted conditions	40 m/min	N
Uni	suitable		
Oil	suitable		
wet maximum	suitable		