Garant

Fluteless machine tap with oil grooves HSS-E-PM Form C 6GX, TiN, M: M2



Order data

| Order number | 139190 M2 |
|--------------|---------------|
| GTIN | 4045197509321 |
| Item class | 11H |

Description

Version:

DIN 2174 (\approx DIN 371 \leq M10; \approx DIN 376 \geq M12). With oil grooves; optimum lubrication effect even in deeper threads. Tolerance class: ISO 3X / 6GX = Oversize 0.02 – 0.04 mm. The innovative polygon form permits a wide application spectrum. The multi-function layer structure achieves maximum service life even in high-tensile materials. Application: For components which are galvanised after threading or which shrink slightly when hardened. Tolerance class: ISO 3X 6GX Thread pitch: 0.4 mm Overall length L: 45 mm Shank \emptyset D_s: 2.8 mm

Shank square □: 2.1 mm

Tapping hole Ø with guide value: 1.85 mm

Technical description

| Number of cutting edges Z | 3 |
|---------------------------|--------|
| Number of clamping slots | 3 |
| Thread Ø | 2 mm |
| Thread pitch | 0.4 mm |
| Shank Ø D _s | 2.8 mm |
| Shank square 🗆 | 2.1 mm |
| Overall length L | 45 mm |

© Hoffmann GmbH Qualitätswerkzeuge

| Tapping hole \varnothing with guide value | 1.85 mm |
|---|---|
| Tolerance class | ISO 3X 6GX |
| Thread depth | 6 mm |
| Thread size | M2 |
| Coating | TiN |
| Thread type | М |
| Flank angle | 60 degrees |
| Tool material | HSS E PM |
| Standard | DIN 2174 |
| Thread standard | DIN 13 |
| Taper lead form | C |
| Shank | Plain shank with h9 |
| Through-coolant | no |
| Application for type of drilling | up to 3×D for blind holes and through holes |
| Cutting direction | right-hand |
| Colour ring | green |
| Type of product | Fluteless tap |