



Machine tap HSS-E-PM Form B 6G, TiAlN, M: M4



Order data

Order number	132725 M4
GTIN	4045197649041
Item class	11H

Description

Version:

Spiral point with oil grooves.

Guide section with oil grooves, but without chip flutes.

Tolerance class: ISO 3 / 6G

Advantage:

Particularly strong, optimal self-guidance.

Application:

For components which are **galvanised** after threading or shrink slightly when hardened.

Note:

NEW GENERATION AVAILABLE!

Recommended successor products are No. 132721-132724.

Thread type: M

Tool material: HSS E PM

Norm: DIN 371

Tolerance class: ISO 3 6G

Thread pitch: 0.7 mm

Overall length L_{tot} : 63 mm

Shank \varnothing : 4.5 mm

Tapping hole \varnothing : 3.3 mm

Technical description

Number of cutting edges Z	2
Thread pitch	0.7 mm
Taper lead angle	50 degrees
Number of clamping slots	2

Tapping hole Ø	3.3 mm
Thread Ø	4 mm
Norm	DIN 371
Shank Ø	4.5 mm
Overall length L _{tot}	63 mm
Tolerance class	ISO 3 6G
Tool material	HSS E PM
Thread depth	12 mm
Thread type	M
Thread size	M4
Coating	TiAlN
Flank angle	60 degrees
Thread standard	DIN 13
Taper lead form	B
Skaft	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for dynamic machining
Colour ring	green