

**Garant****Base rail for tool fitting fixture, Type: 200****Order data**

Order number	358565 200
GTIN	4062406343545
Item class	31P

**Description****Version:**

Modular system consisting of base rails, flexible tool modules for locking on the base rails and a height adjustment/height gauge system.

All components made from high-quality anodised aluminium.

**Advantage:**

- **Clean, tidy workstation – all assembly jigs in one place.**
- **Modular – base rail can be extended at any time through direct attachment.**
- **Flexible – two different tool modules (fixed or pivotable).**
- **Quick and easy handling – locking lever on the tool modules, moving of the setting device on the base rail.**
- **GARANT Easyfix hole pattern on the rear of the base rail – attachment of storage facilities directly on the assembly jig.**
- **100% solid and secure attachment of the arbor – does not wobble, protects the mounting taper.**

**Application:**

- **Assembly/disassembly of all accessory parts of an arbor.**
- **Adopting/copying existing tool lengths.**
- **Measurement of the tool length.**
- **Small parts storage via GARANT Easyfix.**

**Supplied with:**

1× Easyfix wall mounting No. 955825 2, mounting bracket with cover for attaching the base rail, e.g. to a workbench.

**Optional extras:**

Tool module No. 358575 and 358580, height adjustment No. 358585.

**Note:**

The tool mounting device does not replace tool pre-setting.

---

## Technical description

Height	160 mm
Width	40 mm
Length	200 mm
Material	Aluminium
Type of product	Guide rail