

Garant**ANGX 10T308ZEER, HB9740, Type: INOX**

Order data

Order number	213070 INOX
GTIN	4062406355470
Item class	21A

Description

Version:

Double-sided 2-edge inserts. High-performance substrates and innovative cutter geometries guarantee the best possible production results.

Note:

Standard application values for $a_e = 0.5...1 \times D/a_{p,max}$.

Technical description

Type	INOX
Feed f_z per tooth	0.8 mm
Corner radius	0,8 mm
Insert thickness S	3.97 mm
ISO code indexable insert	ANGX 10T308ZEER
Grade	HB9740
Tool material	Carbide

recommended cutting depth $a_{p\max}$	0.8 mm
maximum cutting depth $a_{p\max}$	1 mm
Programming radius at $a_{p\max}$	1.6 mm
Number of changes/inserts	4
Type of product	Indexable insert for milling

User data

	Suitability	V_c	ISO code
INOX < 900 N/mm ²	suitable	180 m/min	M
INOX > 900 N/mm ²	suitable	150 m/min	M
wet maximum	suitable only under restricted conditions		
Air	suitable		