



Morse taper reamer, uncoated, MT: MK2



Order data

| | |
|--------------|---------------|
| Order number | 162500 MK2 |
| GTIN | 4045197089199 |
| Item class | 120 |

Description

Version:

Straight flutes, with plain shank and square drive.

Application:

For reaming Morse taper sockets from taper holes or stepped holes.

Technical description

| | |
|---------------------------------------|--------------|
| Shank square <input type="checkbox"/> | 11 mm |
| Overall length L | 121 mm |
| Flute length L _c | 79 mm |
| Coating | uncoated |
| Tool material | HSS |
| Standard | DIN 204 |
| Through-coolant | no |
| Colour ring | without |
| Type of product | Phillips bit |

User data

| | Suitability | V _c | ISO code |
|--|-------------|----------------|----------|
|--|-------------|----------------|----------|

| | |
|-------------------------------|---|
| Aluminium (short chipping) | suitable |
| Steel < 500 N/mm ² | suitable |
| Steel < 750 N/mm ² | suitable |
| Steel < 900 N/mm ² | suitable only under restricted conditions |
| Oil | suitable |
| dry | suitable only under restricted conditions |