

**Morse taper reamer, uncoated, MT: MK4****Order data**

Order number	162500 MK4
GTIN	4045197089212
Item class	120

Description**Version:**

Straight flutes, with plain shank and square drive.

Application:

For reaming Morse taper sockets from taper holes or stepped holes.

Technical description

Shank square <input type="checkbox"/>	20 mm
Overall length L	179 mm
Flute length L _c	119 mm
Coating	uncoated
Tool material	HSS
Standard	DIN 204
Through-coolant	no
Colour ring	without
Type of product	Phillips bit

User data

	Suitability	V _c	ISO code
--	-------------	----------------	----------

Aluminium (short chipping)	suitable
Steel < 500 N/mm ²	suitable
Steel < 750 N/mm ²	suitable
Steel < 900 N/mm ²	suitable only under restricted conditions
Oil	suitable
dry	suitable only under restricted conditions