

Garant
Machine tap, left-hand thread HSS-E 6H, nitrided and vaporised, M-LH: M14

Order data

Order number	132800 M14
GTIN	4045197072856
Item class	11H

Description
Version:

With strong spiral point. **Guide section with oil grooves**, but without chip flutes.

Advantage:

Particularly strong, optimal self-guidance and no recutting when reversed.

Thread type: M-LH

Tool material: HSS E

Standard: DIN 376

Tolerance class: ISO 2 6H

Thread pitch: 2 mm

Overall length L: 110 mm

Shank $\varnothing D_s$: 11 mm

Shank square \square : 9 mm

Tapping hole \varnothing : 12 mm

Technical description

Thread pitch	2 mm
Tapping hole \varnothing	12 mm
Thread \varnothing	14 mm
Number of cutting edges Z	3
Number of clamping slots	3
Standard	DIN 376
Shank $\varnothing D_s$	11 mm

Overall length L	110 mm
Shank square □	9 mm
Tolerance class	ISO 2 6H
Tool material	HSS E
Thread depth	42 mm
Thread type	M-LH
Thread size	M14 LH
Coating	nitrided and vaporised
Flank angle	60 °
Thread standard	DIN 13
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	left-hand
Type of threading tool	Machine tap for dynamic machining
Colour ring	green
Type of product	Tap

User data

	Suitability	V _c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	13 m/min	N
Steel < 500 N/mm ²	suitable	15 m/min	P
Steel < 750 N/mm ²	suitable	15 m/min	P
Steel < 900 N/mm ²	suitable	15 m/min	P
Steel < 1100 N/mm ²	suitable	6 m/min	P
INOX < 900 N/mm ²	suitable	6 m/min	M
CuZn	suitable only under restricted conditions	13 m/min	N

Uni	suitable
Oil	suitable
wet maximum	suitable only under restricted conditions