

Garant**Machine tap HSS-E Form B, uncoated, MF: 8X0,5****Order data**

Order number	132830 8X0,5
GTIN	4045197072993
Item class	11H

Description**Version:****With spiral point.**

Thread type: MF

Tool material: HSS E

Standard: DIN 374

Tolerance class: ISO 2 6H

Thread pitch: 0.5 mm

Overall length L: 80 mm

Shank $\varnothing D_s$: 6 mmShank square \square : 4.9 mmTapping hole \varnothing : 7.5 mm**Technical description**

Thread pitch	0.5 mm
Number of cutting edges Z	3
Thread \varnothing	8 mm
Number of clamping slots	3
Tapping hole \varnothing	7.5 mm
Shank $\varnothing D_s$	6 mm
Overall length L	80 mm
Shank square \square	4.9 mm
Tolerance class	ISO 2 6H

Tool material	HSS E
Standard	DIN 374
Thread depth	24 mm
Thread type	MF
Thread size	M8×0.5
Coating	uncoated
Flank angle	60°
Thread standard	DIN 13
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap

User data

	Suitability	V _c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	13 m/min	N
Steel < 500 N/mm ²	suitable	15 m/min	P
Steel < 750 N/mm ²	suitable	15 m/min	P
Oil	suitable		
wet maximum	suitable only under restricted conditions		