



## Pneumatic angle grinder with BSP connection thread



### Order data

Order number	079312 G2511-125
GTIN	7322590042868
Item class	03R

### Description

**Version:**

**Powerful angle grinder**, whose operating speed under load scarcely dips when load is applied. The safety starter prevents accidental starting. Angle grinder for one-hand operation in ergonomic lightweight construction with composite casing. The length of the mounting piece is adjustable for easier access to restricted places. With spindle locking and quick adjustment of the guard. **M14 mounting thread.**

**Supplied with:**

Including the necessary coupling adaptors.

**Spare part:**

**Selected service kits:** Sets of replacement parts for most Atlas Copco pneumatic tools can be supplied on request for preventive maintenance and servicing.

### Technical description

Weight	1.77 kg
Manufacturer's designation	G2511-125
maximum vibration to EN	6.5 m/s <sup>2</sup>

maximum air consumption	1020 l/min
recommended hose size (internal Ø)	13 mm
maximum disc Ø	125 mm
Output power	900 W
Operating noise	84 dB(A)
maximum speed	12000 min <sup>-1</sup>
Compressed air connection	3/8 in
Connection thread	BSP
Power supply	Pneumatic
Type of product	Angle grinder