

Garant
Machine tap, TiCN, MF: 3X0,35

Order data

Order number	132860 3X0,35
GTIN	4045197073785
Item class	11H

Description
Recommendation:

For **TOOLOX materials** we recommend **deviating from the DIN data** (see table) by drilling the tapping hole \varnothing **0.05 to 0.3 mm** larger.

Thread type: MF

Tool material: HSS E

Standard: DIN 374

Tolerance class: ISO 2X 6HX

Thread pitch: 0.35 mm

Overall length L: 56 mm

Shank \varnothing D_s: 2.2 mm

Tapping hole \varnothing : 2.65 mm

Technical description

Tapping hole \varnothing	2.65 mm
Thread \varnothing	3 mm
Number of clamping slots	3
Thread pitch	0.35 mm
Number of cutting edges Z	3
Shank \varnothing D _s	2.2 mm
Overall length L	56 mm
Tolerance class	ISO 2X 6HX
Tool material	HSS E

Standard	DIN 374
Thread depth	6 mm
Thread type	MF
Thread size	M3×0.35
Coating	TiCN
Flank angle	60 °
Thread standard	DIN 13
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for dynamic machining
Colour ring	red
Type of product	Tap

User data

	Suitability	V _c	ISO code
Steel < 500 N/mm ²	suitable only under restricted conditions	20 m/min	P
Steel < 750 N/mm ²	suitable only under restricted conditions	19 m/min	P
Steel < 900 N/mm ²	suitable	19 m/min	P
Steel < 1100 N/mm ²	suitable	9 m/min	P
TOOLOX 33	suitable	4 m/min	H
Oil	suitable		
wet maximum	suitable		