

Garant
Machine tap HSS-E, vaporised, MF: 4X0,5

Order data

Order number	132870 4X0,5
GTIN	4045197073976
Item class	11H

Description
Version:
Strong spiral point.

 Guide section **with oil grooves.**

Thread type: MF

Tool material: HSS E

Standard: DIN 374

Tolerance class: ISO 2X 6HX

Thread pitch: 0.5 mm

Overall length L: 63 mm

 Shank $\varnothing D_s$: 2.8 mm

 Shank square \square : 2.1 mm

 Tapping hole \varnothing : 3.5 mm

Technical description

Number of cutting edges Z	3
Number of clamping slots	3
Tapping hole \varnothing	3.5 mm
Thread pitch	0.5 mm
Thread \varnothing	4 mm
Shank $\varnothing D_s$	2.8 mm
Overall length L	63 mm
Shank square \square	2.1 mm

Tolerance class	ISO 2X 6HX
Tool material	HSS E
Standard	DIN 374
Thread depth	12 mm
Thread type	MF
Thread size	M4x0.5
Coating	vaporised
Flank angle	60°
Thread standard	DIN 13
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for dynamic machining
Colour ring	blue
Type of product	Tap

User data

	Suitability	V _c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	13 m/min	N
Steel < 500 N/mm ²	suitable	15 m/min	P
Steel < 750 N/mm ²	suitable	15 m/min	P
Steel < 900 N/mm ²	suitable only under restricted conditions	15 m/min	P
INOX < 900 N/mm ²	suitable	6 m/min	M
CuZn	suitable only under restricted conditions	13 m/min	N
Oil	suitable		

wet maximum

suitable only under
restricted conditions