

Garant
Machine tap HSS-E, vaporised, MF: 5X0,5

Order data

| | |
|--------------|---------------|
| Order number | 132870 5X0,5 |
| GTIN | 4045197073983 |
| Item class | 11H |

Description
Version:
Strong spiral point.

 Guide section **with oil grooves.**

Thread type: MF

Tool material: HSS E

Standard: DIN 374

Tolerance class: ISO 2X 6HX

Thread pitch: 0.5 mm

Overall length L: 70 mm

 Shank $\varnothing D_s$: 3.5 mm

 Shank square \square : 2.7 mm

 Tapping hole \varnothing : 4.5 mm

Technical description

| | |
|----------------------------|--------|
| Tapping hole \varnothing | 4.5 mm |
| Thread \varnothing | 5 mm |
| Number of clamping slots | 3 |
| Number of cutting edges Z | 3 |
| Thread pitch | 0.5 mm |
| Shank $\varnothing D_s$ | 3.5 mm |
| Overall length L | 70 mm |
| Shank square \square | 2.7 mm |

| | |
|----------------------------------|-----------------------------------|
| Tolerance class | ISO 2X 6HX |
| Tool material | HSS E |
| Standard | DIN 374 |
| Thread depth | 15 mm |
| Thread type | MF |
| Thread size | M5×0.5 |
| Coating | vaporised |
| Flank angle | 60° |
| Thread standard | DIN 13 |
| Taper lead form | B |
| Shank | Plain shank with h9 |
| Through-coolant | no |
| Application for type of drilling | up to 3×D for through holes |
| Cutting direction | right-hand |
| Type of threading tool | Machine tap for dynamic machining |
| Colour ring | blue |
| Type of product | Tap |

User data

| | Suitability | V _c | ISO code |
|-------------------------------|---|----------------|----------|
| Aluminium (short chipping) | suitable only under restricted conditions | 13 m/min | N |
| Steel < 500 N/mm ² | suitable | 15 m/min | P |
| Steel < 750 N/mm ² | suitable | 15 m/min | P |
| Steel < 900 N/mm ² | suitable only under restricted conditions | 15 m/min | P |
| INOX < 900 N/mm ² | suitable | 6 m/min | M |
| CuZn | suitable only under restricted conditions | 13 m/min | N |
| Oil | suitable | | |

wet maximum

suitable only under
restricted conditions