

**Garant**
**NC reamer Configurable, uncoated, Nominal Ø DC: 20mm**

**Order data**

Order number	162951 20
GTIN	4045197366382
Item class	110

**Description**
**Version:**
**Reamers finish ground to match your specification.**
**Note:**

 For **fit H7** see No. 162900 and 163000.

For reamers in 1/100 - sizes see No. 162902.

**Technical description**

Feed f in steel < 750 N/mm <sup>2</sup>	0.3 mm/rev.
Shank tolerance	h6
Nominal Ø D <sub>c</sub>	20 mm
Overhang L <sub>1</sub>	146 mm
Shank Ø D <sub>s</sub>	16 mm
Overall length L	195 mm
Flute length L <sub>c</sub>	60 mm
Ø range	19.51 - 20 mm
Number of cutting edges Z	8
Reaming oversize in diameter	0.2 - 0.3 mm
Coating	uncoated
Tool material	HSS E
Standard	Manufacturer's standard

Through-coolant	no
Shank	DIN 1835 A to h6
Application for type of drilling	for through holes
Colour ring	without
Type of product	Phillips bit

### User data

	Suitability	V <sub>c</sub>	ISO code
Aluminium	suitable	20 m/min	N
Aluminium (short chipping)	suitable	20 m/min	N
Steel < 500 N/mm <sup>2</sup>	suitable	15 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	10 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	7 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	5 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable only under restricted conditions	4 m/min	P
INOX < 900 N/mm <sup>2</sup>	suitable	5 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable only under restricted conditions	5 m/min	M
Ti > 850 N/mm <sup>2</sup>	suitable only under restricted conditions	5 m/min	S
GG(G)	suitable only under restricted conditions	5 m/min	K
CuZn	suitable only under restricted conditions	13 m/min	N
Uni	suitable		
Oil	suitable		
wet maximum	suitable		

