

Garant
Spindle, Type: TR16

Order data

| | |
|--------------|---------------|
| Order number | 361119 TR16 |
| GTIN | 4045197809315 |
| Item class | 310 |

Description
Version:

Trapezoidal spindle for optimal force transfer.

The 5-axis vice has a modular design. The key components are the clamping modules No. 361105 – 361110, base rails No. 361115, spindle No. 361119, spindle extensions No. 361120 and the top jaws No. 361123 – 361137.

Application:

TR14 and TR16 **for external clamping**, TR14I and TR16I **for internal clamping**.

Suitable for:

Clamping modules No. 361105 – 361110.

Optional extras:

Spindle extensions No. 361120, torque wrench No. 656050 120. Hexagon screwdriver bit No. 643329 10.

Note:

Spare parts for spindles No. 361176, 361177 and 361178.

Technical description

| | |
|--------------------------|----------|
| AF ₂ | 30 |
| Length L | 229.6 mm |
| AF ₁ | 10 |
| External Ø D | 40 mm |
| suitable for colour code | Xpent1-2 |

| | |
|-----------------|---------|
| Series | Xpent |
| Type of product | Spindle |

Accessories

| | |
|--|----------|
| Nut, Xpent Type 1 | 361177 1 |
| Spindle anchor, Xpent Type 1 | 361176 1 |
| Spindle nut for Xpent, complete with ring Type 1 | 361178 1 |