

Garant
Solid carbide milling cutter Composite, compacting cut, uncoated, Ø h10 DC: 5mm

Order data

Order number	209542 5
GTIN	4062406366131
Item class	100

Description
Version:

Tool cutting edge has been specifically developed further for optimal machining of composite materials.

Overall length similar to **DIN 6527 long**.

Left-hand helix, **compacting cut**. The material is pushed down on to the substrate. Highly suitable for thin materials.

Technical description

Recess Ø D ₁	4.9 mm
Tolerance nominal Ø	h10
No. of teeth Z	8
Overhang length L ₁ incl. recess	19 mm
Direction of infeed	horizontal, oblique and vertical
Corner chamfer angle	45 degrees
Cutting edge Ø D _c	5 mm
Overall length L	57 mm
Shank	DIN 6535 HA to h6
Flute length L _c	13 mm
Corner chamfer width at 45°	0.1 mm

Helix angle	8 degrees
Shank $\varnothing D_s$	6 mm
Feed f_z for slot milling in GRP CRP	0.021 mm
Coating	uncoated
Tool material	Solid carbide
Standard	DIN 6527
Cutting width a_e for milling operation	Full slot cutting depth $1 \times D$
Through-coolant	no
Colour ring	black
Type of product	End / face mill

User data

	Suitability	V_c	ISO code
PVDF GF20	suitable	80 m/min	N
POM GF25	suitable	80 m/min	N
PA 66 GF30	suitable	80 m/min	N
PEEK GF30	suitable	80 m/min	N
PTFE CF25	suitable	80 m/min	N
PEEK CF30	suitable	80 m/min	N
Hybrids	suitable		
Honeycomb sandwich	suitable	165 m/min	N
CRP	suitable	120 m/min	N
GRP, CRP	suitable	120 m/min	N
Graphite	suitable	180 m/min	N
wet maximum	suitable		
dry	suitable		
Air	suitable		

