

**Carbide saw blade, Type: 150X20T34****Order data**

Order number	078212 150X20T34
GTIN	045242568994
Item class	07A

**Description****Version:**

- **Precise tooth geometry for optimum cutting performance.**
- **High-quality carbide and Cermet teeth for outstanding tool life.**
- **Fully hardened and pre-loaded blade for precise cutting.**
- **Deep tooth base for quick and complete chip evacuation.**
- **Internal resin-filled extension slots minimise noise and vibration.**
- **Clean, burr-free, dry cuts reduce the need for post-processing.**
- **Low heat generation – the material can be processed directly after the cut.**

**Application:**

Suitable for metal material.

**Suitable for:**

Cordless circular metal saw no. 078207 size M18FMCS.

Bore Ø: 20 mm

Number of teeth: 34

**Technical description**

Number of teeth	34
-----------------	----

Blade Ø D	150 mm
Bore Ø	20 mm
Type of product	Circular saw blade