

**Garant**
**Machine tap, TiCN, G: G1/2**

**Order data**

Order number	133310 G1/2
GTIN	4045197446206
Item class	11H

**Description**
**Version:**
**With spiral point.**

For use with **emulsion** (fat content minimum 8 %).

**Application:**

**For Whitworth parallel pipe threads** DIN-ISO 228/1 (threads that do not form a seal within the connection).

**Recommendation:**

For **TOOLOX materials** we recommend **deviating from the DIN data** (see table) by drilling the tapping hole  $\varnothing$  **0.05** to **0.3 mm** larger.

Tool material: HSS E

Threads per inch: 14

Thread  $\varnothing$ : 20.96 mm

Overall length L: 125 mm

Shank  $\varnothing$  D<sub>s</sub>: 16 mm

Shank square □: 12 mm

Tapping hole  $\varnothing$ : 19 mm

**Technical description**

Tapping hole $\varnothing$	19 mm
Thread pitch	1.814 mm
Number of clamping slots	3
Thread $\varnothing$	20.96 mm
Number of cutting edges Z	3

Threads per inch	14
Tool material	HSS E
Shank $\varnothing D_s$	16 mm
Overall length L	125 mm
Shank square $\square$	12 mm
Thread depth	41.92 mm
Thread size	G1/2
Coating	TiCN
Thread type	G
Flank angle	55°
Standard	DIN 5156
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for dynamic machining
Colour ring	red
Type of product	Tap

## User data

	Suitability	$V_c$	ISO code
Steel < 500 N/mm <sup>2</sup>	suitable only under restricted conditions	20 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable only under restricted conditions	19 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	19 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	9 m/min	P
TOOLOX 33	suitable	4 m/min	H
Oil	suitable		

wet maximum

suitable