



Pneumatic impact wrench, Type: 0611



Order data

Order number	079204 0611
GTIN	015451722432
Item class	03R

Description

Version:

Impact wrench for the most demanding applications and highest torques. **Exceptionally robust 2-claw impact mechanism** (twin lobe) for a very long working life under rough conditions. The screw tightening phase starts slowly and increases with every impact. **Suitable for all bolt-tightening requirements.** Simple 3-piece design for **very low maintenance requirements.**

Technical description

maximum air consumption	1920 l/min
maximum vibration to EN	18 m/s ²
Tool arbor size	1 in
Operating noise	99 dB(A)
Length	360 mm
recommended hose size (internal Ø)	13 mm
Maximum screw Ø (8.8 - 12.9)	M36
Tool arbor drive profile	Square
Manufacturer's designation	0611
maximum speed	3500 min ⁻¹

Weight	10.4 kg
Torque range	1220 - 2440 Nm
Compressed air connection	1/2 in
Connection thread	NPT
Type of product	Screwdriver