



## Pneumatic impact wrench, Type: 6120



### Order data

Order number	079204 6120
GTIN	015451729462
Item class	03R

### Description

#### Version:

**Impact wrench for the most demanding applications** and highest torques. **Exceptionally robust 2-claw impact mechanism** (twin lobe) for a very long working life under rough conditions. The screw tightening phase starts slowly and increases with every impact. **Suitable for all bolt-tightening requirements.** Simple 3-piece design for **very low maintenance requirements.**

### Technical description

Torque range	815 - 2710 Nm
Length	420 mm
Maximum screw $\varnothing$ (8.8 - 12.9)	M36
recommended hose size (internal $\varnothing$ )	13 mm
maximum speed	3500 min <sup>-1</sup>
Tool arbor size	1,1/2 in
Weight	15.7 kg
Manufacturer's designation	6120
maximum air consumption	1698 l/min

Operating noise	97 dB(A)
maximum vibration to EN	21.8 m/s <sup>2</sup>
Tool arbor drive profile	Square
Compressed air connection	1/2 in
Connection thread	NPT
Type of product	Screwdriver