

Garant
Machine tap, uncoated, UNF: 3/8-24

Order data

Order number	133400 3/8-24
GTIN	4045197074782
Item class	11H

Description
Version:
With spiral point.
Application:
For UNF uniform fine threads ASME – B1.1.

Thread type: UNF

Tool material: HSS E

Standard: DIN 374

Threads per inch: 24

Thread Ø: 9.53 mm

Overall length L: 100 mm

 Shank Ø D_s: 7 mm

Shank square □: 5.5 mm

Tapping hole Ø: 8.5 mm

Technical description

Number of cutting edges Z	3
Tapping hole Ø	8.5 mm
Thread Ø	9.53 mm
Threads per inch	24
Number of clamping slots	3
Standard	DIN 374
Tool material	HSS E

Shank $\varnothing D_s$	7 mm
Overall length L	100 mm
Shank square \square	5.5 mm
Thread depth	28.59 mm
Thread pitch	1.058 mm
Thread type	UNF
Thread size	3/8-24 UNF
Coating	uncoated
Flank angle	60 °
Tolerance class	2B
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap

User data

	Suitability	V_c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	13 m/min	N
Steel < 500 N/mm ²	suitable	15 m/min	P
Steel < 750 N/mm ²	suitable	15 m/min	P
Oil	suitable		
wet maximum	suitable only under restricted conditions		

