

Garant

Solid carbide HPC deep-hole drill plain shank DIN 6535 HA 16×D, TiAlN, Ø DC h7: 5,8mm



Order data

Order number	123688 5,8
GTIN	4045197355324
Item class	11E

Description

Version:

Spiral fluted, with **4 guide chamfers** and internal cooling channels. New generation of high performance deep hole drills in the HPC range.

With 135° point angle and special **h7 cutting edge tolerance** for optimum generation of a deep hole.

High roundness and alignment accuracy of the deep hole.

Note:

Flute length $L_c = L_2 + 1.5 \times D_c$.

For process reliability when using the 16×D deep hole drill, an initial centre drilling with No. 121068 – 121130 or 4×D pilot drilling operation with pilot drill No. 122736 is necessary. For deep holes greater than 20×D, a pilot hole to the maximum drilling depth with pilot drill No. 122736 is absolutely essential. **The generation of a pilot hole improves process reliability.** See also pages 129/130.

Standard: Manufacturer's standard

Tolerance nominal Ø: h7

Number of cutting edges Z: 2

recommended maximum drilling depth L_2 : 99.3 mm

Tolerance nominal Ø: h7

Overall length L: 150 mm

Shank Ø D_s : 6 mm

Feed f in steel < 900 N/mm²: 0.12 mm/rev.

Technical description

Number of cutting edges Z	2
Flute length L_c	108 mm

Nominal $\varnothing D_c$	5.8 mm
Feed f in steel < 900 N/mm ²	0.12 mm/rev.
Tolerance nominal \varnothing	h7
Shank $\varnothing D_s$	6 mm
Overall length L	150 mm
Standard	Manufacturer's standard
recommended maximum drilling depth L ₂	99.3 mm
Coating	TiAlN
Tool material	Solid carbide
Version	16xD
Point angle	135 °
Shank	DIN 6535 HA to h6
Through-coolant	yes, with 40 bar
Machining strategy	HPC
Pilot drill required	yes, pilot drill
Colour ring	green
Type of product	Jobber drill

User data

	Suitability	V _c	ISO code
Steel < 500 N/mm ²	suitable	110 m/min	P
Steel < 750 N/mm ²	suitable	95 m/min	P
Steel < 900 N/mm ²	suitable	95 m/min	P
Steel < 1100 N/mm ²	suitable	95 m/min	P
Steel < 1400 N/mm ²	suitable	75 m/min	P
INOX < 900 N/mm ²	suitable	55 m/min	M
INOX > 900 N/mm ²	suitable only under restricted conditions	50 m/min	M
GG(G)	suitable	100 m/min	K

Uni	suitable
wet maximum	suitable