



Machine tap, TiN, UNF: 5/16-24



Order data

Order number	133405 5/16-24
GTIN	4045197532831
Item class	11H

Description

Version:

With spiral point and special TiN coating, for stainless and acid-resistant steels.

For use with **emulsion** (fat content minimum 8 %).

Application:

For UNF uniform fine threads ASME – B1.1.

Thread type: UNF

Tool material: HSS E

Norm: DIN 374

Threads per inch: 24

Thread Ø: 7.94 mm

Overall length L_{tot} : 90 mm

Shank Ø: 6 mm

Shank square: 4.9 mm

Tapping hole Ø: 6.9 mm

Technical description

Tapping hole Ø	6.9 mm
Thread Ø	7.94 mm
Threads per inch	24
Number of clamping slots	3
Taper lead angle	50 degrees
Number of cutting edges Z	3
Norm	DIN 374

Tool material	HSS E
Shank Ø	6 mm
Overall length L _{tot}	90 mm
Shank square	4.9 mm
Thread depth	23.82 mm
Thread pitch	1.058 mm
Thread type	UNF
Thread size	5/16-24
Coating	TiN
Flank angle	60 degrees
Tolerance class	2B
Taper lead form	B
Skaft	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for dynamic machining
Colour ring	blue