

**KUB Pentron® indexable drill Plain shank, 2×D, Ø Dc: 40mm****Order data**

Order number	236614 40
GTIN	4047109277649
Item class	24P

Description**Version:****Bore tolerance:** $\varnothing D - 0.1 / + 0.2$

- **Very high performance and long tool life thanks to optimised base body strength and special surface treatment.**
- **Best dimensional accuracy under very difficult drilling conditions.**
- **Stock costs reduced because internal and external inserts are identical.**
- **Offset-axis drilling is possible up to $V_{\max} = 0.25$ mm. Maximum $\varnothing = D + 0.5$ mm achievable by offsetting.**

Application:

- **Under extreme machining conditions.**

With indexable inserts No. 236605 – 236610.

Supplied with:

Clamp screws (without indexable inserts).

Note:

Version 2×D and 3×D with ABS® also available on request in imperial sizes.

Version with PSC shank available on request.

Technical description

ISO code indexable insert	SOGX 120408 42-...
Shank $\varnothing D_s$	40 mm
Reach L_1	80 mm
Number of cutting edges Z	1
Shank length L_s	68 mm

Pack of insert screws	239652 20IP (6.3 Nm)
Series	KUB Pentron®
Nominal Ø D	40
Overhang L _A	108 mm
Drill depth for indexable insert drill up to	2×D
Shank	ISO 9766
Use for drilling	limited centre drilling
Use for drilling	limited convexity
Use for drilling	limited cross-drilling
Use for drilling	limited drilling through a stack
Use for drilling	limited drilling with oblique exit
Use for drilling	limited cross-drilling
Through-coolant	yes
Machining strategy	HPC
Type of product	Indexable drill

Accessories

8 mm blade with magnet with 1/4 inch bit holder overall length 50 mm	659874 50
Torque screwdriver with scale, to take interchangeable blades maximum torque 1600 cNm	659906 1600
Torx Plus® insert screw set 10 pieces Drive 20IP	239652 20IP
PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 20IP	674252 20IP
Torque screwdriver with scale, to take interchangeable blades maximum torque 1600 cNm	659957 1600