



Machine tap, uncoated, UNF: 12-28



Order data

Order number	133402 12-28
GTIN	4045197594761
Item class	12H

Description

Version:

With spiral point.

Application:

For UNF uniform fine threads ASME – B1.1.

Thread type: UNF

Tool material: HSS E

Standard: DIN 374

Threads per inch: 28

Thread Ø: 5.49 mm

Overall length L: 80 mm

Shank Ø D_s: 4 mm

Shank square □: 3 mm

Tapping hole Ø: 4.7 mm

Technical description

Thread Ø	5.49 mm
Threads per inch	28
Tapping hole Ø	4.7 mm
Number of cutting edges Z	3
Number of clamping slots	3
Standard	DIN 374
Tool material	HSS E
Shank Ø D _s	4 mm

Overall length L	80 mm
Shank square □	3 mm
Thread depth	16.44 mm
Thread pitch	0.907 mm
Thread type	UNF
Thread size	12-28 UNF
Coating	uncoated
Flank angle	60°
Tolerance class	2B
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap

User data

	Suitability	V _c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	13 m/min	N
Steel < 500 N/mm ²	suitable	15 m/min	P
Steel < 750 N/mm ²	suitable	15 m/min	P
Oil	suitable		
wet maximum	suitable only under restricted conditions		

