

Garant**Machine tap, nitrided, Tr: TR14X3****Order data**

Order number	133490 TR14X3
GTIN	4045197533043
Item class	11H

Description**Version:****Profile correct for NC**, with divided envelope cut.**Lead chamfer:** ≈ 20 turns. **With 25° left-hand flutes**, right-hand cutting.**Advantage:****Suitable for reversing.****Note:****For use on synchronised spindles.**

The lead must be machine driven.

Technical description

Number of cutting edges Z	3
Tapping hole \varnothing	11.25 mm
Number of clamping slots	3
Thread pitch	3 mm
Shank $\varnothing D_s$	10 mm
Overall length L	145 mm
Shank square \square	8 mm
Thread depth	16.87 mm
Thread size	14
Coating	nitrided
Thread type	TR

Flank angle	30 degrees
Tool material	HSS E
Standard	Manufacturer's standard
Tolerance class	DIN 103 7H
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 1.5xD for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for dynamic machining
Colour ring	green
Type of product	Tap

User data

	Suitability	V _c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	7 m/min	N
Steel < 500 N/mm ²	suitable	7 m/min	P
Steel < 750 N/mm ²	suitable	5 m/min	P
Steel < 900 N/mm ²	suitable	3 m/min	P
INOX < 900 N/mm ²	suitable	3 m/min	M
GG(G)	suitable	7 m/min	K
CuZn	suitable	7 m/min	N
Uni	suitable		
Oil	suitable		
wet maximum	suitable		