



Plain shank thread mill 2×D, TiAlN, M: M10



Order data

Order number	139650 M10
GTIN	4045197081933
Item class	11J

Description

Version:

Corrected thread profile for milling **exact internal threads** (ensure stable clamping conditions). **Internal coolant feed.**

Note:

NEW GENERATION AVAILABLE!

Recommended successor product is No. 139640.

Through-coolant: yes

No. of teeth Z: 3

Drilling depth for blind and through holes: 2.0×D

Thread pitch: 1.5 mm

Hole Ø d₁: 8 mm

maximum insertion depth l₁: 20.2 mm

Shank length L_s: 36 mm

Overall length L_{tot}: 70 mm

Technical description

Thread pitch	1.5 mm
Feed f _z in steel < 750 N/mm ²	0.035 mm
maximum insertion depth l ₁	20.2 mm
Number of clamping slots	3
No. of teeth Z	3
Drilling depth for blind and through holes	2.0×D
Hole Ø d ₁	8 mm

Shank Ø	8 mm
Overall length L _{tot}	70 mm
Shank length L _s	36 mm
Through-coolant	yes
Hole Ø	8 mm
Full profile	yes
Thread depth	20 mm
Thread size	10
Coating	TiAlN
Thread type	M
Thread type	M-LH
Flank angle	60 degrees
Tool material	Solid carbide
Thread standard	DIN 13
Skaft	DIN 6535 HA with h6
Application for type of drilling	up to 2×D for blind holes and through holes
Shank tolerance	h6
Colour ring	green