

Garant**Machine tap HSS-E-PM, Hard chrome, M: M6****Order data**

Order number	134270 M6
GTIN	4045197075277
Item class	11H

Description**Version:****Hard chrome-plated surface** for reduced edge build-up and increased tool life.**Application:**Suitable for materials with tensile strength **up to maximum 450N/mm²**.

Thread type: M

Tool material: HSS E PM

Standard: DIN 371

Tolerance class: ISO 2 6H

Thread pitch: 1 mm

Overall length L: 80 mm

Shank $\varnothing D_s$: 6 mmShank square \square : 4.9 mmTapping hole \varnothing : 5 mm**Technical description**

Number of clamping slots	3
Tapping hole \varnothing	5 mm
Thread \varnothing	6 mm
Thread pitch	1 mm
Number of cutting edges Z	3
Standard	DIN 371
Shank $\varnothing D_s$	6 mm
Overall length L	80 mm

Shank square <input type="checkbox"/>	4.9 mm
Tolerance class	ISO 2 6H
Tool material	HSS E PM
Thread depth	12 mm
Thread type	M
Thread size	M6
Coating	Hard chrome
Flank angle	60°
Thread standard	DIN 13
Taper lead form	C
Helix angle	40°
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for dynamic machining
Colour ring	yellow
Type of product	Tap

User data

	Suitability	V _c	ISO code
Alu plastics	suitable	28 m/min	N
Aluminium (short chipping)	suitable	28 m/min	N
Alu > 10% Si	suitable	23 m/min	N
Steel < 500 N/mm ²	suitable only under restricted conditions	27 m/min	P
CuZn	suitable only under restricted conditions	28 m/min	N
Oil	suitable		

wet maximum

suitable