

## Garant

### Solid carbide HPC deep-hole drill plain shank DIN 6535 HA 30×D, TiAlN, Ø DC h7: 4,8mm



#### Order data

|              |               |
|--------------|---------------|
| Order number | 123695 4,8    |
| GTIN         | 4045197320506 |
| Item class   | 11E           |

#### Description

##### Version:

Spiral fluted, with **4 guide chamfers** and internal cooling channels. New generation of high performance deep hole drills in the HPC range.

**With 135° point angle** and special **h7 cutting edge tolerance** for optimum generation of a deep hole.

**High roundness and alignment accuracy of the deep hole.**

##### Note:

Flute length  $L_c = L_2 + 1.5 \times D_c$ .

For process reliability when using the 16×D deep hole drill, an initial centre drilling with No. 121068 – 121130 or 4×D pilot drilling operation with pilot drill No. 122736 is necessary. For deep holes greater than 20×D, a pilot hole to the maximum drilling depth with pilot drill No. 122736 is absolutely essential. **The generation of a pilot hole improves process reliability.** See also pages 129/130.

Standard: Manufacturer's standard

Tolerance nominal Ø: h7

Number of cutting edges Z: 2

recommended maximum drilling depth  $L_2$ : 157.8 mm

Tolerance nominal Ø: h7

Overall length L: 215 mm

Shank Ø  $D_s$ : 6 mm

Feed f in steel < 900 N/mm<sup>2</sup>: 0.1 mm/rev.

#### Technical description

|   |             |
|---|-------------|
| Feed f in steel < 900 N/mm <sup>2</sup> | 0.1 mm/rev. |
| Number of cutting edges Z               | 2           |

|  |                         |
|--|-------------------------|
| Nominal $\varnothing D_c$                | 4.8 mm                  |
| Flute length $L_c$                       | 165 mm                  |
| Tolerance nominal $\varnothing$          | h7                      |
| Shank $\varnothing D_s$                  | 6 mm                    |
| Overall length L                         | 215 mm                  |
| Standard                                 | Manufacturer's standard |
| recommended maximum drilling depth $L_2$ | 157.8 mm                |
| Coating                                  | TiAlN                   |
| Tool material                            | Solid carbide           |
| Version                                  | 30xD                    |
| Point angle                              | 135°                    |
| Shank                                    | DIN 6535 HA to h6       |
| Through-coolant                          | yes, with 40 bar        |
| Machining strategy                       | HPC                     |
| Pilot drill required                     | yes, pilot drill        |
| Colour ring                              | green                   |
| Type of product                          | Jobber drill            |

## User data

|                                | Suitability                               | $V_c$    | ISO code |
|--------------------------------|---|----------|----------|
| Steel < 500 N/mm <sup>2</sup>  | suitable                                  | 90 m/min | P        |
| Steel < 750 N/mm <sup>2</sup>  | suitable                                  | 75 m/min | P        |
| Steel < 900 N/mm <sup>2</sup>  | suitable                                  | 75 m/min | P        |
| Steel < 1100 N/mm <sup>2</sup> | suitable                                  | 75 m/min | P        |
| Steel < 1400 N/mm <sup>2</sup> | suitable                                  | 60 m/min | P        |
| INOX < 900 N/mm <sup>2</sup>   | suitable                                  | 45 m/min | M        |
| INOX > 900 N/mm <sup>2</sup>   | suitable only under restricted conditions | 40 m/min | M        |
| GG(G)                          | suitable                                  | 80 m/min | K        |

|             |          |
|-------------|----------|
| Uni         | suitable |
| wet maximum | suitable |