

**Garant**
**Solid carbide HPC deep hole drill plain shank DIN 6535 HA 30×D, TiAlN, Ø DC h7: 2,4mm**

**Order data**

Order number	123695 2,4
GTIN	4045197320391
Item class	11E

**Description**
**Version:**

Spiral fluted, with **4 guide chamfers** and internal cooling channels. New generation of high performance deep hole drills in the HPC range.

**With 135° point angle** and special **h7 cutting edge tolerance** for optimum generation of a deep hole.

**High roundness and alignment accuracy of the deep hole.**

**Note:**

Flute length  $L_c = L_2 + 1.5 \times D_c$ .

For process reliability when using the 16×D deep hole drill, an initial centre drilling with No. 121068 – 121121 or 4×D pilot drilling operation with pilot drill No. 122736 is necessary. For deep holes greater than 20×D, a pilot hole to the maximum drilling depth with pilot drill No. 122736 is absolutely essential. **The generation of a pilot hole improves process reliability.** See also pages 140/141.

**Technical description**

Number of cutting edges Z	2
Feed f in steel < 900 N/mm <sup>2</sup>	0.06 mm/rev.
Nominal Ø D <sub>c</sub>	2.4 mm
Flute length L <sub>c</sub>	90 mm
Tolerance nominal Ø	h7
Shank Ø D <sub>s</sub>	4 mm
Overall length L	138 mm

Standard	Manufacturer's standard
recommended maximum drilling depth L <sub>2</sub>	86.4 mm
Coating	TiAlN
Tool material	Solid carbide
Version	30xD
Point angle	135 degrees
Shank	DIN 6535 HA to h6
Through-coolant	yes, with 40 bar
Machining strategy	HPC
Pilot drill required	yes, pilot drill
Colour ring	green
Type of product	Jobber drill

## User data

	Suitability	V <sub>c</sub>	ISO code
Steel < 500 N/mm <sup>2</sup>	suitable	90 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	75 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	75 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	75 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable	60 m/min	P
INOX < 900 N/mm <sup>2</sup>	suitable	45 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable only under restricted conditions	40 m/min	M
GG(G)	suitable	80 m/min	K
Uni	suitable		
wet maximum	suitable		