

Garant**Machine tap, uncoated, M: M2,6****Order data**

Order number	134600 M2,6
GTIN	4045197075383
Item class	11H

Description**Version:****Sturdy design, with 15 – 20° right-hand helix.**

Size M2.6 has the old DIN profile.

Thread type: M

Tool material: HSS E

Standard: DIN 371

Tolerance class: ISO 2 6H

Thread pitch: 0.45 mm

Overall length L: 50 mm

Shank $\varnothing D_s$: 2.8 mmShank square \square : 2.1 mmTapping hole \varnothing : 2.1 mm**Technical description**

Thread pitch	0.45 mm
Tapping hole \varnothing	2.1 mm
Thread \varnothing	2.6 mm
Number of clamping slots	2
Number of cutting edges Z	2
Standard	DIN 371
Shank $\varnothing D_s$	2.8 mm
Overall length L	50 mm

Shank square <input type="checkbox"/>	2.1 mm
Tolerance class	ISO 2 6H
Tool material	HSS E
Thread depth	5.2 mm
Thread type	M
Thread size	M2.6
Coating	uncoated
Flank angle	60°
Thread standard	DIN 13
Taper lead form	D
Helix angle	15-20°
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap

User data

	Suitability	V _c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	13 m/min	N
Steel < 500 N/mm ²	suitable	15 m/min	P
Steel < 750 N/mm ²	suitable	15 m/min	P
Oil	suitable		
wet maximum	suitable only under restricted conditions		

