



Pneumatic straight die grinder G2414, collets Ø 6 mm short, Type: S250



Order data

Order number	079447 S250
GTIN	7322590019839
Item class	03R

Description

Version:

Powerful and robust smooth-running straight die grinders. The safety switch prevents accidental switching on. Application-optimised maximum speeds between **8500 and 25,000 rpm.**

Short design, length 215 mm.

Collet Ø 6mm.

Supplied with:

Including the necessary coupling adaptors.

Spare part:

Selected service kits:

Sets of replacement parts for most Atlas Copco pneumatic tools can be supplied on request for preventive maintenance and servicing.

Technical description

maximum speed	25000 min ⁻¹
Manufacturer's designation	G2414 S250
maximum vibration to EN	< 2.5 m/s ²
Output power	950 W

recommended hose size (internal Ø)	13 mm
maximum air consumption	870 l/min
Operating noise	85 dB(A)
Weight	0.78 kg
Compressed air connection	3/8 in
Connection thread	BSP
Type of product	Straight die grinder

Accessories

Collet for straight grinder Collet Ø 6 mm	079459 6
-------------------------------------------	----------