

## Garant

### Solid carbide NC machine reamer, uncoated, Nominal $\varnothing$ DC: 5,99mm



#### Order data

Order number	164340 5,99
GTIN	4045197093615
Item class	11P

#### Description

##### Version:

**Version suitable for NC** similar to DIN 8093 **with straight shank  $\varnothing$**  for **standard chucking** especially in **hydraulic chucks** or **high precision collet chucks**. This ensures **the highest concentricity**.

##### Tolerance specifications:

Size 0.6 – 0.9: Manufacturing or cutting edge tolerance **0/+0.004 mm**.

Size 0.98 – 20: Reamer manufacturing or cutting edge tolerance to DIN1420 for **H7 bore tolerance**.

**No need to procure special collets when using GARANT-NC reamers.** With long flutes and left-hand helix.

##### Application:

For reaming through holes, as the chips are evacuated in the cutting direction. Lead taper is suitable also for blind holes.

##### Note:

For reamers like No. 164340 and 164341 but with other diameters and fits see No. 164344 and 164345.

#### Technical description

Shank tolerance	h6
Nominal $\varnothing$ D <sub>c</sub>	5.99 mm
Feed f in steel < 1100 N/mm <sup>2</sup>	0.12 mm/rev.
Overhang L <sub>1</sub>	51 mm
Shank $\varnothing$ D <sub>s</sub>	6 mm
Overall length L	93 mm

Flute length $L_c$	26 mm
Number of cutting edges Z	6
Tolerance	H7
Reaming oversize in diameter	0.1 - 0.2 mm
Coating	uncoated
Tool material	Solid carbide
Standard	Manufacturer's standard
Through-coolant	no
Shank	DIN 6535 HA with h6
Application for type of drilling	for through holes
Colour ring	green
Type of product	Phillips bit

## User data

	Suitability	$V_c$	ISO code
Aluminium	suitable	35 m/min	N
Aluminium (short chipping)	suitable	30 m/min	N
Steel < 500 N/mm <sup>2</sup>	suitable	20 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	13 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	10 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	8 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable	6 m/min	P
INOX < 900 N/mm <sup>2</sup>	suitable only under restricted conditions	10 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable only under restricted conditions	8 m/min	M
Ti > 850 N/mm <sup>2</sup>	suitable	8 m/min	S
GG(G)	suitable	8 m/min	K
CuZn	suitable	20 m/min	N

Uni	suitable
wet maximum	suitable