

Garant

Solid carbide HPC deep hole drill plain shank DIN 6535 HA 50×D, TiAlN, Ø DC: 6,8mm


Order data

Order number	123750 6,8
GTIN	4045197498366
Item class	11E

Description
Version:

Spiral fluted, with **4 guide chamfers** and internal cooling channels. New generation of high performance deep hole drills in the HPC range. **With 135° point angle** and special **fg6 cutting edge tolerance** for optimum generation of deep holes. **High roundness and alignment accuracy of the deep hole.**

Note:

Flute length $L_c = L_2 + 1.5 \times D_c$.

To achieve good process reliability with 40×D and 50×D deep hole drills, it is absolutely essential to drill a pilot hole to the maximum drilling depth with a pilot drill No. 122736 and a 20×D co-pilot hole with a co-pilot drill No. 123691.

The generation of a pilot hole improves process reliability. See also pages 140/141.

Technical description

Number of cutting edges Z	2
Flute length L_c	380 mm
Feed f in steel < 900 N/mm ²	0.12 mm/rev.
Nominal Ø D_c	6.8 mm
Tolerance nominal Ø	fg6
Shank Ø D_s	8 mm
Overall length L	425 mm
Standard	Manufacturer's standard

recommended maximum drilling depth L ₂	369.8 mm
Coating	TiAlN
Tool material	Solid carbide
Version	50×D
Point angle	135 degrees
Shank	DIN 6535 HA to h6
Through-coolant	yes, with 40 bar
Machining strategy	HPC
Pilot drill required	yes, pilot and co-pilot drill
Colour ring	green
Type of product	Jobber drill

User data

	Suitability	V _c	ISO code
Steel < 500 N/mm ²	suitable	65 m/min	P
Steel < 750 N/mm ²	suitable	50 m/min	P
Steel < 900 N/mm ²	suitable	50 m/min	P
Steel < 1100 N/mm ²	suitable	50 m/min	P
Steel < 1400 N/mm ²	suitable	45 m/min	P
INOX < 900 N/mm ²	suitable	35 m/min	M
INOX > 900 N/mm ²	suitable only under restricted conditions	30 m/min	M
GG(G)	suitable	55 m/min	K
Uni	suitable		
wet maximum	suitable		