

Garant
Machine tap, vaporised, M: M2

Order data

Order number	135300 M2
GTIN	4045197076335
Item class	11H

Description
Version:

With strong right-hand chip flutes, for optimum swarf evacuation.

Recommendation:

For **TOOLOX materials we recommend deviating from the DIN data** (see table) by drilling the tapping hole \varnothing **0.05** to **0.3 mm** larger.

Thread type: M

Tool material: HSS E

Standard: DIN 371

Tolerance class: ISO 2 6H

Thread pitch: 0.4 mm

Overall length L: 45 mm

Shank \varnothing D_s: 2.8 mm

Shank square □: 2.1 mm

Tapping hole \varnothing : 1.6 mm

Technical description

Number of cutting edges Z	2
Number of clamping slots	2
Thread pitch	0.4 mm
Thread \varnothing	2 mm
Tapping hole \varnothing	1.6 mm
Standard	DIN 371
Shank \varnothing D _s	2.8 mm

Overall length L	45 mm
Shank square □	2.1 mm
Tolerance class	ISO 2 6H
Tool material	HSS E
Thread depth	4 mm
Thread type	M
Thread size	M2
Coating	vaporised
Flank angle	60°
Thread standard	DIN 13
Taper lead form	C
Helix angle	40°
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2xD for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for dynamic machining
Colour ring	red
Type of product	Tap

User data

	Suitability	V _c	ISO code
Steel < 500 N/mm ²	suitable only under restricted conditions	15 m/min	P
Steel < 750 N/mm ²	suitable only under restricted conditions	15 m/min	P
Steel < 900 N/mm ²	suitable	15 m/min	P
Steel < 1100 N/mm ²	suitable	6 m/min	P
TOOLOX 33	suitable	3 m/min	H
Oil	suitable		

wet maximum

suitable only under
restricted conditions