

Garant
Machine tap, vaporised, M: M24

Order data

Order number	135300 M24
GTIN	4045197076441
Item class	11H

Description
Version:

With strong right-hand chip flutes, for optimum swarf evacuation.

Recommendation:

For **TOOLOX materials we recommend deviating from the DIN data** (see table) by drilling the tapping hole \varnothing **0.05 to 0.3 mm** larger.

Thread type: M

Tool material: HSS E

Standard: DIN 376

Tolerance class: ISO 2 6H

Thread pitch: 3 mm

Overall length L: 160 mm

Shank \varnothing D_s: 18 mm

Shank square □: 14.5 mm

Tapping hole \varnothing : 21 mm

Technical description

Thread \varnothing	24 mm
Number of clamping slots	5
Thread pitch	3 mm
Number of cutting edges Z	5
Tapping hole \varnothing	21 mm
Standard	DIN 376
Shank \varnothing D _s	18 mm

Overall length L	160 mm
Shank square □	14.5 mm
Tolerance class	ISO 2 6H
Tool material	HSS E
Thread depth	48 mm
Thread type	M
Thread size	M24
Coating	vaporised
Flank angle	60 °
Thread standard	DIN 13
Taper lead form	C
Helix angle	40 °
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2xD for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for dynamic machining
Colour ring	red
Type of product	Tap

User data

	Suitability	V _c	ISO code
Steel < 500 N/mm ²	suitable only under restricted conditions	15 m/min	P
Steel < 750 N/mm ²	suitable only under restricted conditions	15 m/min	P
Steel < 900 N/mm ²	suitable	15 m/min	P
Steel < 1100 N/mm ²	suitable	6 m/min	P
TOOLOX 33	suitable	3 m/min	H
Oil	suitable		

wet maximum

suitable only under
restricted conditions