

**Garant****Machine tap, vaporised, M: M2,5****Order data**

Order number	134851 M2,5
GTIN	4045197350824
Item class	11H

**Technical description**

Tapping hole $\varnothing$	2.05 mm
Number of cutting edges Z	2
Thread $\varnothing$	2.5 mm
Thread pitch	0.45 mm
Number of clamping slots	2
Standard	DIN 371
Shank $\varnothing D_s$	2.8 mm
Overall length L	50 mm
Shank square $\square$	2.1 mm
Tolerance class	ISO 2 6H
Tool material	HSS E
Thread depth	7.5 mm
Thread type	M
Thread size	M2.5
Coating	vaporised
Flank angle	60 degrees
Thread standard	DIN 13

Taper lead form	C
Helix angle	40 degrees
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap

### User data

	Suitability	V <sub>c</sub>	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	13 m/min	N
Steel < 500 N/mm <sup>2</sup>	suitable	15 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	15 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	15 m/min	P
CuZn	suitable only under restricted conditions	13 m/min	N
Oil	suitable		
wet maximum	suitable only under restricted conditions		