



Pneumatic straight die grinder G2424, collets Ø 6 mm long, Type: S150



Order data

| | |
|--------------|---------------|
| Order number | 079448 S150 |
| GTIN | 7322590019877 |
| Item class | 03R |

Description

Version:

Powerful and robust smooth-running straight die grinders. The safety switch prevents accidental switching on. Application-optimised maximum speeds between **8500 and 25,000 rpm.**

With long, slim spindle, ideal for holes length 317 mm.

Collet Ø 6mm.

Supplied with:

Including the necessary coupling adaptors.

Spare part:

Selected service kits:

Sets of replacement parts for most Atlas Copco pneumatic tools can be supplied on request for preventive maintenance and servicing.

Technical description

| | |
|------------------------------------|------------------------|
| Manufacturer's designation | G2424 S150 |
| Output power | 750 W |
| recommended hose size (internal Ø) | 13 mm |
| Weight | 0.96 kg |
| maximum vibration to EN | < 2.5 m/s ² |

| | |
|---------------------------|-------------------------|
| maximum speed | 15000 min ⁻¹ |
| maximum air consumption | 432 l/min |
| Operating noise | 76 dB(A) |
| Compressed air connection | 3/8 in |
| Connection thread | BSP |
| Type of product | Straight die grinder |

Accessories

| | |
|---|----------|
| Collet for straight grinder Collet Ø 6 mm | 079459 6 |
|---|----------|