

HOLEX®
Die 6g, M: M20

Order data

| | |
|--------------|---------------|
| Order number | 140320 M20 |
| GTIN | 4045197083340 |
| Item class | 12K |

Description
Version:

Closed, pre-slit form. **≥ M3 with tapered lead chamfer** on both sides for easy start to the threading action and clean swarf evacuation in the direction of cutting. **1¾ turns lead chamfer.**

Thread type: M

Flank angle: 60 degrees

Tool material: HSS

Norm: EN 22568

Tolerance class: DIN 13 6g

Pitch: 2.5 mm

External Ø: 45 mm

Height: 18 mm

Technical description

| | |
|------------|--------|
| Pitch | 2.5 mm |
| Height | 18 mm |
| External Ø | 45 mm |

| | |
|-------------------|------------|
| Tolerance class | DIN 13 6g |
| Thread size | 20 |
| Thread type | M |
| Flank angle | 60 degrees |
| Tool material | HSS |
| Norm | EN 22568 |
| Cutting direction | right-hand |