

**Garant****Plastic grinding bodies Taper, medium, Type: 1919K****Order data**

|              |               |
|--------------|---------------|
| Order number | 501565 1919K  |
| GTIN         | 4062406372811 |
| Item class   | 58F           |

**Description****Version:**

**Plastic grinding bodies** (aluminium oxide abrasive grit bonded in plastic) have a **low density** and a **softer substrate**. This enables **gentle processing** and the **grinding bodies do not become clogged**. Significantly **lower abrasive effect** compared to ceramic grinding bodies. Finish grinding to polishing.

**Application:**

For **fine grinding** and for **light deburring work** on soft materials such as **aluminium, copper** and **plastic**. Achieves very high surface quality with a matt sheen.

**Taper** form for workpieces with **bores and contours**.

**Technical description**

|                   |        |
|-------------------|--------|
| Grit designation  | medium |
| Shape description | Taper  |
| Height            | 19 mm  |
| Width             | 19 mm  |

|                        |                             |
|------------------------|-----------------------------|
| Series                 | GMT                         |
| Grinding media         | regular aluminium oxide (A) |
| Grinding medium code   | A                           |
| Product name attribute | medium                      |
| Contents               | 25 kg                       |
| Type of product        | Grinding body               |

### User data

|              | Suitability | V <sub>c</sub> | ISO code |
|--------------|-------------|----------------|----------|
| Alu Mg       | geeignet    |                |          |
| CuZn         | geeignet    |                |          |
| Plastic, GRP | geeignet    |                |          |
| wet maximum  | geeignet    |                |          |